

LUMILUX COMBI LED-F

Batten luminaires for direct connection



Areas of application

- Offices, hotels, living areas
- Corridors, entrances, foyers, stairwells, elevators
- Counters, reception and waiting areas, wardrobes, mirrors
- Shops, changing rooms, shop windows
- Cove lighting, even in tight spaces
- Shelves, furniture integration or under cabinet mounting
- Kitchens, workspaces
- Single luminaire as architectural design element

Product benefits

- Slender, general-purpose LED batten luminaire
- Fixed connection with rear cable entry
- Very easy and time-saving installation
- Suitable for use even in tight spaces thanks to small housing cross-section
- Expandable with LUMILUX COMBI LED-E to trunking of up to 13 luminaires (up to 15 m)
- No dark spots with trunking

Product features

- Integrated ECG
- High-quality appearance thanks to anodized aluminum housing and matt diffuser
- No visible differences in light color between luminaires thanks to fine binning
- High luminous efficacy: up to 100 lm/W



Product family datasheet

Technical data

Product description	Electrical data			Photometrical data			Light technical data	Dimensions & weight		
	Nominal wattage	Nominal voltage	Mains frequency	Color temperature	Luminous flux	Light color (designation)	Light distribution	Length	Width	Height
LUMILUX COMBI LED -F 10 W 3000 K	10.0 W	220...240 V	50/60 Hz	3000 K	980 lm	Warm white	Symmetric	580.0 mm	25.0 mm	44.0 mm
LUMILUX COMBI LED -F 10 W 4000 K	10.0 W	220...240 V	50/60 Hz	4000 K	1100 lm	Cool white	Symmetric	580.0 mm	25.0 mm	44.0 mm
LUMILUX COMBI LED -F 18 W 3000 K	18.0 W	220...240 V	50/60 Hz	3000 K	1900 lm	Warm white	Symmetric	1180 mm	25.0 mm	44.0 mm
LUMILUX COMBI LED -F 18 W 4000 K	18.0 W	220...240 V	50/60 Hz	4000 K	2050 lm	Cool white	Symmetric	1180 mm	25.0 mm	44.0 mm

Product description	Colors & materials			Temperatures & operating conditions	Capabilities		Certificates & standards	
	Body material	Product color	Cover material	Ambient temperature range	Type of installation	Type of connection	Protection class	Type of protection
LUMILUX COMBI LED -F 10 W 3000 K	Aluminum	Silver	Polycarbonate (PC)	-20...+40 °C	Surface-mounted	Terminal, 2-pole	II	IP20
LUMILUX COMBI LED -F 10 W 4000 K	Aluminum	Silver	Polycarbonate (PC)	-20...+40 °C	Surface-mounted	Terminal, 2-pole	II	IP20
LUMILUX COMBI LED -F 18 W 3000 K	Aluminum	Silver	Polycarbonate (PC)	-20...+40 °C	Surface-mounted	Terminal, 2-pole	II	IP20
LUMILUX COMBI LED -F 18 W 4000 K	Aluminum	Silver	Polycarbonate (PC)	-20...+40 °C	Surface-mounted	Terminal, 2-pole	II	IP20

Product description	Country specific categorizations
	Order reference
LUMILUX COMBI LED -F 10 W 3000 K	72821
LUMILUX COMBI LED -F 10 W 4000 K	72822
LUMILUX COMBI LED -F 18 W 3000 K	72823
LUMILUX COMBI LED -F 18 W 4000 K	72824

Product family datasheet

Equipment / Accessories

- Complete mounting and connecting accessories included
-

Application advice

For more detailed application information and graphics please see product datasheet.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.