



PUSHBUTTON, D=70MM 1NC/1NC 20A,
2BUTTON RED+GREEN LAMP 230V

Similar to image

Technical data:

Nature of fluorescent material		glow lamp
Number of NC contacts		0
type of voltage		AC
Number of change-over switches		0
Mounting depth	mm	70
Number of NO contacts		2
Number of pitch units for width		1
Current / rated value	A	20
Color / of the button		others
Product component / Signal lamp		Yes
Operating voltage / rated value	V	400
Active power / for filament lamp load / maximum	W	0.17
Protection class IP		IP20
Holder design / for fluorescent material		others
Color / of the lens		others

Certificates/approvals: