

Technical data sheet

Article number:
151-04529

EC1-3SVDHC6-7

Product Group	Fixing element for solar cables
Product Family	EdgeClip series for solar panels
Material	Polyamide 11 (PA11), Steel C75S (C75S)
Colour	Black (BK)
Fixation Method	EdgeClip, sideways
Height (H)	13.2 mm
Length (L)	23.1 mm
Length (L2)	18.6 mm
Operating Temperature	-40 °C to +85 °C
Package Content	100 pcs.
Panel Thickness	3.0 mm
Panel Thickness max.	1.0 - 3.0 mm
Panel Thickness min. (metric)	1.0 mm
Recyclate content	0 %
ROHS compliant	Yes
UV-Stabilised	Yes [Raw Material based]
Width (W)	14.0 mm

HF ✓

RoHS ✓