



ENGLISH

Datasheet

RS PRO PCL Conical Nozzle Blow Gun

Stock number: 1899351



Manufactured from chemical and impact resistant acetal resin, this Conical Nozzle Blowgun is suitable for use with both air and water.

PCL's Conical Nozzle Blowgun is supplied in a blister pack.



Features & Benefits

- Ergonomically designed handle, for comfort in use
- Valve allows trigger-adjustable airflow
- Supplied in blister pack



Specifications

Maximum Supply Pressure 10 bar / 140 psi

Connection 1/4 Female

Air Flow 270 l/min / 9.3 cfm

Temperature Range 0 to 80 °C

Grip Style Pistol

Nozzle Style Conical



Safety Information

- Outlet pressure on blowguns should not exceed 2bar / 28lbf/in². It is therefore recommended that an in-line regulator is fitted to your air supply to ensure this.