



### Main

Range of product	Altivar
Range compatibility	Altivar 312 Altivar 61 Altivar Lift Altivar 32 Altivar Machine ATV320 Altivar 312 Solar Altivar 212 Altivar 71 Altivar 61Q Altivar 71Q
Accessory / separate part category	Display and signalling accessories
Accessory / separate part type	Display terminal
Accessory / separate part destination	Variable speed drive
Product specific application	To control, adjust and configure the drive To save and download configurations To display the current values
IP degree of protection	IP54

### Complementary

Mounting location	On the door of an enclosure
Language	Italian English French Spanish German Chinese
Messages display capacity	8 lines
Pixel resolution	240 x 160
Net weight	0.145 kg

### Environment

Ambient air temperature for operation	-15...50 °C
---------------------------------------	-------------

### Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
-------------------	--

[EU RoHS Declaration](#)

Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>

**Contractual warranty**

Warranty	18 months
----------	-----------