



182.72.104.66NKNadellager

Needle roller bearings NK8/12-TV-XL (Series NK)

light series

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

Fw	8 mm
D	15 mm
C	12 mm
rmin	0,3 mm
m	8,7 g Mass
Cr	4450 N Basic dynamic load rating, radial
C0r	4100 N Basic static load rating, radial
Cur	690 N Fatigue limit load, radial
nG	32500 1/min Limiting speed
nB	37000 1/min Reference speed
With closing rings, without lubrication hole and without lubrication groove.	
G8X15X3	Suitable sealing ring
SD8X15X3	Suitable sealing ring

