

# TEST REPORT



Manufacturer : tesa SE  
Hugo-Kirchberg-Str. 1  
22848 Norderstedt

tesa product no. : tesa 51408

tesa product : high temperature resistant masking tape

Remarks :

Test criterion	Unit	from / to	Value*	tesa test method
Total Thickness	µm	65 ± 5	65	J0PMC002
Breakdown Voltage	V	> 6,000	6110	DIN EN 60243-1

\*non-specific values

We confirm that the supplied material meets the quality standard of this product.

Date of creation

20.09.2019

This certificate of analysis has been produced electronically and is valid without a signature.  
These data do not relieve the customer from making his own quality incoming inspection of goods, particularly in consideration of influences regarding transport or temporary storage which are not under our control.  
Furthermore, our general terms of sales are applicable.

This document is controlled via tesa Document Management System – online document takes precedence!