

### **FEATURES**

- Thermoplastic handles
- Zinc plated steel or stainless steel studs
- Matte black finish
- Can short term withstand +170°C
- Resistant to most chemicals, UV light and water absorption (1.5% max)
- Working temperature range of -20°C to +110°C

# RS PRO Black 4-Arm Clamping Knob, M10

RS Stock No.: 702-7746



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



**Product Description** 

Knobs are used in a wide variety of applications in our day-to-day lives and perform many functions, from being used as fixed handles to being used to tighten, loosen, adjust and push other components or pieces of equipment. They are used in various applications, from industrial and construction machinery to audio and visual equipment.

**Female Knobs:** Zinc-plated steel: M8 x 12 (RS <u>7027715</u>), M8 x 15 (RS <u>7027718</u>), M10 x 15 (RS <u>7027712</u>), M12 x 15 (RS <u>7027721</u>).

Stainless steel: M8 x 15 (RS <u>7027740</u>), M10 x 15 (RS <u>7027759</u>), M12 x 15 (RS <u>7027752</u>). **Male Knobs:** Zinc-plated steel: M6 x 25mm (RS <u>7027692</u>), M8 x 20mm (RS <u>7027695</u>), M8 x 30mm (RS <u>7027699</u>), M8 x 25mm (RS <u>7027709</u>), M10 x 25mm (RS <u>7027702</u>), M12 x 30mm (RS <u>7027706</u>).

Stainless steel: M6 x 25mm (RS <u>7027737</u>), M8 x 20mm (RS <u>7027730</u>), M8 x 30mm (RS <u>7027734</u>), M8 x 25mm (RS <u>7027743</u>), M10 x 25mm (RS <u>7027746</u>).

Through-Thread Knobs: Zinc-plated steel: M8 x 12 (RS 7027724), M10 x 15 (RS 7027728).

Stainless steel: M8 x 12 (RS 7027756), M10 x 15 (RS 7027765).

#### **General Specifications**

Thread	M10
Knob Shape	4-Arm
Mounting Type	Threaded Stud
Insert Material	Stainless Steel
Colour	Black
Finish	Matte
Application	Access doors, Drawers & panels (domestic and industrial), Clamps and fixtures, Industrial machinery, Food preparation machinery, Medical furniture

#### **Mechanical Specifications**

Thread Diameter	10mm
Thread Length	25mm
Knob Diameter	60mm
Hole Diameter	16mm
Hole Length	29mm

## Knobs



