

NORTON

SAINT-GOBAIN

Reshaping
your
world.



R222 - Handy Rolls

Handy Rolls Norton-R222-38x25m#60

Artical Number: 63642531824

EAN: 3157620183235



Description

R222 handy rolls are designed for manual applications. The high flexibility of the cloth in combination with the wide grit range, from coarse to fine, provides an excellent tool for a variety of applications including deburring, rust removal and finishing metal.

Features & Benefits

J-weight cloth backing

Premium aluminium oxide abrasive

Dispenser unit

Application Data

Material Application: NON-FERROUS
Machine: Manual application
Process: Sanding

Equipments:



Technical Data

MarketingCAP:	R222	Length:	
BackingMaterial:	Light Cotton J	Width:	38 mm
Grit:	60		
Color:	Maroon		
CoatedShape:	Rolls Trimmed		
CoatedSubShape:	Handyroll		
		Shape:	

Logistic Data

Naked Product Weight:	0.504 kg	Packed Product Dimension:	250 mm x 865 mm x 45 mm
Naked Product Dimension:	38x25m	pack Qty (parts per pack):	1 pc
Units per part:	1 pc	Packed Product Weight:	0.023 kg