

## har-port USB 3.0 A-A PFT cable 1,0m



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 45 452 1931                                                                |
| Specification      | har-port USB 3.0 A-A PFT cable 1,0m                                           |
| HARTING eCatalogue | <a href="https://harting.com/09454521931">https://harting.com/09454521931</a> |

### Identification

|               |                    |
|---------------|--------------------|
| Category      | Connectors         |
| Series        | har-port           |
| Element       | Service interfaces |
| Specification | USB 3.0            |

### Version

|                 |                                |
|-----------------|--------------------------------|
| Cable length    | 1 m                            |
| Connection type | Type A jack - type A connector |
| Fixing          | Screwable in cover plates      |

### Technical characteristics

|                                        |                |
|----------------------------------------|----------------|
| Ambient temperature                    | -25 ... +70 °C |
| Mating cycles                          | ≥1,500         |
| Degree of protection acc. to IEC 60529 | IP20           |

### Material properties

|                             |                |
|-----------------------------|----------------|
| Material (hood/housing)     | Polyamide (PA) |
| Colour (hood/housing)       | silver         |
| RoHS                        | compliant      |
| ELV status                  | compliant      |
| China RoHS                  | e              |
| REACH Annex XVII substances | Not contained  |
| REACH ANNEX XIV substances  | Not contained  |



Pushing Performance  
Since 1945

Material properties

|                       |               |
|-----------------------|---------------|
| REACH SVHC substances | Not contained |
|-----------------------|---------------|

Specifications and approvals

|           |        |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

Commercial data

|                                |                                      |
|--------------------------------|--------------------------------------|
| Packaging size                 | 1                                    |
| Net weight                     | 90 g                                 |
| Country of origin              | Germany                              |
| European customs tariff number | 85444290                             |
| GTIN                           | 5713140163355                        |
| eCl@ss                         | 27060304 Appliance cord (data cable) |
| ETIM                           | EC002599                             |
| UNSPSC 24.0                    | 43202222                             |