

Acces. Special Cable Clamp EMC PG 36, Ir



Image is for illustration purposes only. Please refer to product description.

Part number	09 62 000 5011
Specification	Acces. Special Cable Clamp EMC PG 36, Ir
HARTING eCatalogue	https://harting.com/09620005011

Identification

Category	Accessories
Type of accessory	Cable gland
Description of the accessory	EMC version

Technical characteristics

Wrench size	50
Degree of protection acc. to IEC 60529	IP68
Size	Pg 36
Clamping range	24 ... 28 mm
Shielding diameter	18 ... 25.5 mm

Material properties

Material (cable glands)	Metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead 2-(2'-Hydroxy-3'-tert-butyl-5'-methylphenyl)-5-chlorobenzotriazole (UV-326)
California Proposition 65 substances	Yes



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Lead
--------------------------------------	------

Commercial data

Packaging size	10
Net weight	196 g
Country of origin	Germany
European customs tariff number	74122000
GTIN	5713140072930
eCl@ss	27140803 Cable gland EMC (electrical installation)
ETIM	EC000441
UNSPSC 24.0	39121431