



Multi Purpose



Light Duty

Industrial safety gloves with 30% greater breathability and a dirt-masking dark liner

- **Considered aesthetics:** HyFlex® 11-801 industrial gloves' darker liner helps extend wear life by masking dirt
- **Elevated comfort:** Their nitrile foam coating also makes them 30% more breathable than comparable gloves, for less irritable daily wear
- **Enhanced grip:** The same nitrile coating enhances grip, making them ideal in dry and slightly oily environments
- **Everyday usability:** HyFlex® 11-801 safety gloves' ZONZ™ Comfort Fit Technology relieves tension and delivers a tailored feel
- **Improved durability:** These HyFlex® gloves also possess ANSI/EN-compliant abrasion resistance, for longer wear
- **Guaranteed skin-friendliness and cleanliness:** They are Dermatest®-approved for skin-friendliness, and benefit from an impurity-extracting proprietary washing process



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Chemical

Applications

- Picking, fastening components
- Adjusting systems and screwing
- Fastening components, parts
- Loading and unloading trucks and vehicles
- Handling incoming goods
- Loading trucks & vehicles
- Product shipping, transport and delivery
- Lock smith

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-801

Improved design delivers enhanced comfort in a dirt masking color

Key Features

- **Darker liner:** For safety gloves suited to dirty or oily conditions
- **Breathable nitrile coating:** PPE gloves that offer all-day comfort
- **ZONZ™ Comfort Fit Technology:** Reduced tension, greater usability

Technologies



DMF free



Performance Standards & Regulatory Compliance

REACH Compliant



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 11-801	Finishing: Palm Coated Coating Material: Foam Nitrile Liner Material: Nylon Cuff Style: Knitwrist	15	6, 7, 8, 9, 10, 11	192-265 mm/ 7.55-10.51 inches	Black	• 12 pairs in a bag; 12 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

