

NORTON

SAINT-GOBAIN

Reshaping
your
world.**R222 - Handy Rolls****Handy Rolls Norton-R222-50x25m#150**

Artical Number: 63642531810

EAN: 3157620182108

**Description**

R222 handy rolls are designed for manual applications. The high flexibility of the cloth in combination with the wide grit range, from coarse to fine, provides an excellent tool for a variety of applications including deburring, rust removal and finishing metal.

Features & Benefits

J-weight cloth backing

Premium aluminium oxide abrasive

Dispenser unit

Application Data

Material Application: NON-FERROUS
Machine: Manual application
Process: Sanding

Equipments:

**Technical Data**

MarketingCAP:	R222	Length:	
BackingMaterial:	Light Cotton J	Width:	50 mm
Grit:	150		
Color:	Maroon		
CoatedShape:	Rolls Trimmed		
CoatedSubShape:	Handyroll		
		Shape:	

Logistic Data

Naked Product Weight:	0.066 kg	Packed Product Dimension:	182 mm x 616 mm x 60 mm
Naked Product Dimension:	50x25m	pack Qty (parts per pack):	1 pc
Units per part:	1 pc	Packed Product Weight:	0.042 kg