



Cut



Heavy Duty

Robust abrasion, cut and heat-resistant gloves, delivering a good grip and flexibility

- **Increased comfort and dexterity:** These industrial gloves feature a seamless liner and knitted wrist that deliver good sensitivity, fit and cushioning
- **Heightened durability and protection:** EDGE[®] 48-703 safety work gloves offer a high level of abrasion resistance and medium cut protection, and their leather palm boasts a good grip in dry and slightly oily environments
- **Enhanced defenses:** In addition, these protective gloves provide EN 407 level 1 contact heat protection, making them ideal for workers handling hot equipment, parts and objects



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Oil and gas

Applications

- Handling slightly oily metal parts and sheets
- Stamping press shop
- Primary assembly

Key Features

- **Seamless design and knitted wrist:** Combining comfort and dexterity
- **Leather palm:** For hand protection gloves with a good grip performance
- **Thermal resistance:** Ability to confidently handle hot components

Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4X43D

EN 407



X1XXXX

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
EDGE® 48-703	Finishing: Leather Palm Coating Material: Leather Liner Material: Polyethylene, Fiber glass Cuff Style: Knitwrist	13	7, 8, 9, 10	230-265 mm, 9.05-10-43 inches	Grey	12 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551