

# Product Specification PDF

Date	<b>Correct as of 10th Jan 2025</b>
Brand	<b>C.K Tools</b>
Product	<b>T3120A 2045</b>
Description	<b>SDS Drill Bit 20x350x450mm</b>
Barcode	<b>5013969250114</b>
Commodity code	<b>8207503000</b>
Country of origin	<b>CN</b>



Features & Benefits	~ Tungsten carbide tipped with optimized geometry for drilling concrete and stone ~ Vacuum brazed tips for durability ~ Ground flutes designed for optimum debris removal ~ SDS-plus shank ~ Diameter: 20 mm ~ Working length: 350 mm ~ Total length: 450 mm
Health & Safety	Users and bystanders are advised to wear safety goggles
Warranty	C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	10	25
Width mm	20	20	100	100
Depth mm	450	500	450	550
Height mm	20	20	100	250
Weight	395.8	399.8	4048	10.7
Packaging Information	Card use	0	0	Case
	Card gms	0	0	500
	Plastic use	Grade 4 LDPE	poly bag	-
	Plastic gms	8	10	50
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0