

#### **FEATURES**

- Stainless steel superior corrosion resistance
- Suited to higher pressure and temperature applications
- Investment casting
- Blow-out proof stem
  protects the operator
- Anti-static device (option)

# RS PRO Stainless Steel High Pressure Ball Valve 2 in BSPP 2 Way

RS Stock No.: 499-2846



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



### **Product Description**

Introducing the RS PRO general purpose manual ball valve designed for industrial applications. Manual ball valves are used to operate shut off valves which control water flow and pressure.

Available in a variety of sizes:

499-2789 - 1/4 inch BSPP F-F

499-2795 - 1/2 inch BSPP F-F

499-2802 - 3/4 inch BSPP F-F

499-2818 - 1 inch BSPP F-F

499-2824 - 1-1/4 inch BSPP F-F

499-2830 - 1-1/2 inch BSPP F-F

499-2846 - 2 inch BSPP F-F

#### **General Specifications**

Threaded Connection	2 in BSPP
Attachment Type	Threaded
Body Material	ASTM A351-CF8M
Thread Size	2in
Safe For Use With	Gas, Oil, Water
Ball Material	ASTM A351-CF8M
Thread Standard	BSPP
Handle Material	Stainless Steel
Туре	2 Way
Application	Heating systems; Water treatment; Liquid flow control

#### **Mechanical Specifications**

Connection Size	50.8mm				
Torque	8.8Nm				
Weight	1.4kg				



## **Operation Environment Specifications**

Working Temperature	-20°C to 200°C		
Maximum Working Pressure	68 bar		

## **Approvals**

Compliance/Certifications	ISO-5211









DN 50



		ITE	м		PARTS			MATERIAL		
	1			BODY				ASTM A351-CF8M		
	2		RETAINER				ASTM A351-CF8M			
	3		BODY SEAL				PTFE			
	4		BALL			ASTM A351-CF8M				
5		BALL SEAT				PTFE / RTFE				
	6		STEM			ASTM A276-316				
	7		FLAT WASHER			AISI 304				
8		SPRING WASHER			AISI 304					
9		STEM NUT			AISI 304					
10		THRUST WASHER			PTFE					
		11		PACKING			PTFE			
12			HANDLE			STAINLESS STEEL				
								STAINLESS ST	EEL	
13		LATCH LOCK			STAINLESS STEEL					
14		HANDLE SLEEVE			PVC					
d	L	L1	Н	H1	W		S	Torque (N-m)	Weight	
32	100	49	68.5	51	160.5		8	8.8	1.4	