



Cut



Medium Duty

Touchscreen-friendly polyurethane gloves that offer heightened comfort and dexterity

- **Heightened tactility:** Carbon inserts in the HyFlex® 11-729's index finger and thumb increase these industrial gloves' tactile sensitivity, ensuring touchscreen compatibility
- **Enhanced dexterity:** Spandex® in these industrial safety gloves' coating and liner enables hand protection with increased dexterity and reduced hand fatigue
- **Added protection:** INTERCEPT™ Cut Resistance Technology's blend of yarns and fibers ensures some cut protection
- **Improved grip:** HyFlex® 11-729 industrial working gloves' polyurethane coating ensures good grip performance, for secure handling in dry or slightly oily conditions
- **Elevated comfort:** HPPE Lycra® also present in the liner offers workers increased comfort by alleviating repetitive strain



Industries

- Automotive
- Transportation
- Construction
- Glass manufacturing
- Machinery and Equipment
- Maintenance
- Metal fabrication

Applications

- Aeronautics
- Assembling metal parts and components
- Assembly of white goods
- Glass repair and replacement
- Handling sharp or irregular metal pieces
- Press injection molding

Key Features

- **Carbon insert in index finger and thumb:** Touchscreen compatibility
- **Spandex® in liner and coating:** For PPE gloves with ample dexterity
- **INTERCEPT™ Cut Resistance:** Enhanced hand protection

Technologies



INTERCEPT™
Cut Resistance Technology



Touchscreen Compatible

Performance Standards & Regulatory Compliance



EN388: 2016



4342B

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-729	Finishing: Palm dipped Coating Material: Polyurethane Liner Material: HPPE, Nylon, Spandex Cuff Style: Long knitwrist	13	6, 7, 8, 9, 10, 11, 12	270-320 mm	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.