

1507 XL 01210

Mobile workbench extra-wide drawers

Code	ETIM
3127869	EC002224
EAN	UNSPSC
4010886955901	56-12-18-02
Country of origin	eCl@ss
Germany	21-10-02-00
Customs tariff number	
94032080	



Article description

- Body:
- Dimensions: H 985 x W 1200 x D 625 mm
- 30 mm thick multiplex laminated beech wood board, surface additionally protected by linseed oil varnish
- Worktop offset to the rear allows flush parking against the wall
- One drawer unit in trolley width
- Manoeuvrable and easy to steer with drive/steer handle
- Side walls with Euro perforation 10 x 38 mm for attaching hooks and tools
- Ready to take up tool holder KL-5501-20 for installation of spring compressor KL-5501
- Safety through heel protection for persons
- Sheet steel, corrosion and scratch-resistant, powder-coated, GEDORE blue
- Drawers:
- Central locking with cylinder lock
- Wide drawers (W 998 x D 474 mm) with full extension, removable
- Single pull-out stop prevents more than one drawer from being opened, one-hand operation
- Guide rails with ball bearings
- Load capacity per drawer 70 kg • Sheet steel, corrosion and scratch-resistant, powder-coated, GEDORE blue
- GEDORE High-performance chassis:
- Total load capacity 1000 kg, in mobile operation 750 kg
- 2 GEDORE heavy-duty wheels with roller bearings (fixed castors, 200 mm)
- 2 GEDORE easy-running wheels with ball bearings (swivel castors, 125 mm), both with total brake each
- Even under maximum loads, the GEDORE trapezoidal axle construction ensures: smooth running, maneuverability and directional stability
- Ideal for equipping with GEDORE tool modules (1500 ES/1500 CT) maximum 9 pieces 1/3 modules possible per drawer
- Further drawer versions upon request
- Special colours and designs on request
- Delivery without tools and accessories

Article information

Contents (Qty of pieces)	1	Load capacity per drawer [kg]	70 kg
Net weight [kg]	130 kg	Drawer type	1x Type 2, H. = 101,5 mm 2x Type 3, H. = 155 mm 1x Type 4, H. = 208 mm
Total width [mm]	1.200 mm	Thickness (e.g. workplate)	30 mm
Total height [mm]	985 mm	Worktop dimensions	1200 x 635 x 30 mm
Surface	powder-coated	Fixed roller diameter (2x)	200
Total depth [mm]	635 mm	Swivel castor diameter with brakes (2x)	125
Material	sheet steel	Single pull-out stop	yes
Colour	GEDORE blue, RAL 5017	Number of wheels	4
Dimension (L x W x H)	985 mm x 1.200 mm x	Working height	985
Load capacity kg	750 kg	Static load carrying capacity [kg]	1000 kg
Number of drawers	4		