



Main

| | |
|------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range | Linergy |
| Product name | Linergy TR |
| Product or component type | Cover plate |
| Device short name | TRA |
| Accessory / separate part category | Insulation accessory |
| Product compatibility | TRV screw terminal - passthrough terminal block TRV screw terminal - protective earth terminal block TRV screw terminal - blade disconnect terminal block |
| Thickness | 2.2 mm |

Complementary

| | |
|-----------------------------|-------------------------------------------------------------------------------------|
| Cable cross section | 10 mm ² 4 mm ² 2.5 mm ² 6 mm ² |
| Number of connections | 2 |
| Number of measurement input | 1 2 |
| Quantity per set | Set of 50 |
| Net weight | 2.4 g |
| Colour | Blue |

Packing Units

| | |
|------------------|----------|
| Package 1 Weight | 6 g |
| Package 2 Weight | 126 g |
| Package 3 Weight | 2.476 kg |

Offer Sustainability

| | |
|----------------------------|-------------------------------------------------------------------------------------------------------------|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|