




Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought





TE Part #3-2232546-3
GI2.5 HDR ASS 3P RED NO BOSS
TAPE



TE Part #1-1986711-5
SCREWLESS, SW,15P,5.0 PCB



TE Part #2-2291728-1
D3200M FMLB REC HSG 12P SSKEY




TE Part #7-2176392-3
RQ 1206 750K 0.1% 10PPM 5K RL




TE Part #6-292171-6
CT POST HDR ASSY 6P IN TUBE NA



TE Part #9-1617542-8
JMGSC-5LW=M39016/41-049L



TE Part #5-2176392-7
RQ 1206 511K 0.1% 10PPM 5K RL



TE Part #2-1734598-4
1.25 WTB HDR DIP, L=2.3, 4P



TE Part #Y5015-000000100138
FIXED SOCKET CONNECTOR



TE Part #YDIV44E15-35SNC001
RECP ASSY

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-582118-2_AP.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-582118-2_AP.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-582118-2_AP.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS

English

Product Specifications



Application Specification

English

Test Probe Receptacle Contacts

English