



ENGLISH

Datasheet

RS Pro Mechanical HVAC Thermostat, RS Pro KLR-E 7611, SPDT 10A

RS Stock No: **425-6487**



Product Details

RS Pro mechanical HVAC thermostat has a reversing valve via an automatic changeover contact. This device effectively controls split air conditioners, split units without reversing valve and 4-Pipe fan coil systems. It includes second (boost) heating stage, which activates when primary stage is insufficient to maintain the temperature level.

Features and Benefits

- Wall mounted
- Controls split air conditioners
- Includes two heating stages



Specifications:

Contact Rating	10 A
Maximum Temperature	+30°C
Minimum Temperature	+5°C
Supply Voltage	230 V ac
Switch Configuration	SPDT
Temperature Range	+5 to +30°C