

accessory LED lamp 025, AC connecting cable, AWG16, with socket, UL



Model		
product brand name		SIVACON
product designation		AC socket with cable 2 m
design of the product		AWG 16 with socket
type of light source		LED
Protection class		
protection class IP		IP20
Product details		
product component		
● ON/OFF switch		
● light sensor		
● socket outlet		
product feature magnetic		No
Connections		
type of electrical connection for through-wiring		Plug-in connection
Mechanical Design		
fastening method		miscellaneous
material		plastic
Approvals Certificates		
General Product Ap- proval	other	Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR2210-2B>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR2210-2B>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR2210-2B

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

