


紧急停止 开关

84-5321.2B40

分销方
Rs-online



<https://rs-online.eao.com/component/84-5321.2...>

您的产品:



84-5321.2B40
紧急停止开关

正面

正面尺寸:	Ø 32 mm
正面形式:	圆形

安装

安装开孔:	Ø 22.3 mm
安装类型:	面板安装

操作

灯罩颜色:	红色
灯罩材质:	塑料，符合 UL 94 V0
灯罩发光:	发光
灯罩形状:	蘑菇头
灯罩透明度:	不透明
灯罩:	圆
开关位置显示环:	绿色
发光颜色:	红色

电气特性

开关电压和电流:

开关交流额定值 带银触点 (镀金)		
负载类型 AC-15, 根据 EN IEC 60947-5-1		
电压	120 VAC	240 VAC
电流	3 A	1,5 A
开关直流额定值 带银触点 (镀金)		
负载类型 DC-13 根据 EN IEC 60947-5-1		
NO 触点	NC 触点	NO/NC 触点
(48 VA)	(60 VA)	
12 VDC/2.0 A	12 VDC/2.5 A	125 VDC/0.22 A
24 VDC/2.0 A	24 VDC/2.5 A	250 VDC/0.11 A
48 VDC/1.0 A	48 VDC/1.25 A	
60 VDC/0.8 A	60 VDC/1.0 A	

触点:	1 NC
工作电压:	5 - 30 V DC (LED)
工作电流:	9,7 - 12,4 mA
额定工作电压 Ue :	250 VAC/DC 根据 EN IEC 60947-1
额定耐冲击电压:	4 kV, 根据 EN IEC 60947-1
额定绝缘电压 Ui :	250 V 根据 EN / IEC 60947-1
额定电流短路:	1 000 A, 短路设备类型6 A gG (EN 60947-5-1)
建议的最小工作参数:	银触点 (镀金) 电压1 VAC/DC 电流1 mA
开关额定值:	250 V AC @ 1,5 A
电气寿命:	50 000 cycles of operation
耐电强度:	500 VAC, 50 Hz, 1 min, (DIN IEC 60512-2)
过电压类别:	III, 根据 EN / IEC 60947-1
污染等级:	3,根据 EN IEC 60947-1
防护等级:	II, 根据 EN / IEC 60947-5
标准:	根据 EN 60947-5-1, EN 60947-5-5, DIN EN ISO 13850, EN IEC 60204
热电流 Ith :	5 A

机械特性

端子:	扁平带状电缆 300 mm
触点材质:	金
开关动作:	自锁
开关系统:	慢动开关元件
释放方式:	旋转解锁
机械寿命:	250 000 次
操作力:	20 N ±4 N

操作行程: 约 4 mm

拧紧力矩: 固定0.8 Nm

重量: 0.036 kg

环境条件

正面**IP**等级: IP65, IP66, IP67, 符合DIN EN 60529标准

IP保护: IP20 后部

IK保护: 符合IEC 62262的IK07标准

工作温度: - 25 °C ... + 70 °C

储存温度: - 25 °C ... + 85 °C

抗冲击能力: 最大 150 m / s², 脉宽 11 ms, 3轴 (半正弦曲 EN IEC 60068-2-27)

耐振动能力: 最大 50 m / s², 10 Hz ... 500 Hz, 10 次, 3轴 (正弦曲线 EN IEC 60068-2-6)

耐候性: 湿热循环, 96 h, + 25 °C/97 %, + 55 °C/93 % 相对湿度, 根据 EN IEC 60068-2-30
恒温, 56 d, + 40 °C/93 %相对湿度, 根据 EN IEC 60068-2-78
盐雾:96小时, +35°C的氯化钠溶液, 根据EN IEC 60068-2-11
干热:96小时, +70°C, 根据EN IEC 60068-2-2
低温:96小时, -40°C(根据EN IEC 60068-2-1)
参照标准EN IEC 60068-2-5进行的模拟太阳辐射测试SA2与耐候性测试SB1

证书

标准认证: CB (IEC 60947-5-1. IEC60947-5-5), CCC, EN ISO 13850, UL NISD

符合标准: CE, UKCA, 2006 / 42 / EC (MD), 2011 / 65 / EC (RoHS)

REACH: REACH compliant

RoHS: RoHS compliant

其他

简述: 紧急停止开关, Ø 22.3 mm, Ø 32 mm, 蘑菇头, 发光, 红色, 塑料, 符合 UL 94 V0, 不透明, 圆形, 1 NC, 自锁, 扁平带状电缆 300 mm, IP65, IP66, IP67, 符合DIN EN 60529标准, 旋转解锁, 红色

材质: 塑料, 符合 UL 94 V0


外壳颜色: 黄色

外壳材质: 塑料,根据 UL 94 V0

提示: 顺时针旋转解锁
发光二极管制造过程引起的亮度和波长变化可能会导致与照明度有关的细微差异
完全符合EN IEC 60947-5-5
红色灯罩
标准型: 扁平带状电缆长度300 mm或快插端子2.8 mm x 0.5 mm

描述组件:

接线图:




Technical drawing of a cable assembly. The drawing includes a cross-section of a cable on the left, showing a central conductor and an outer jacket. To the right is a side view of a cable with a braided shield, labeled with 'A' and 'B'. Below this are two tables of dimensions.

Dimensions	Values
10-15	11/15 ± 27/34
2.0	11/15 ± 27/34
	30/75 ± 30

Dimensions	Values
10-15	11/15 ± 27/34
2.0	11/15 ± 27/34
	10/15 ± 11/15

安装开孔:

[illegible]