

Technical data sheet

Article number:
924-00503

BLU0.75

Product Group	Un-Insulated Bootlace Ferrules
Product Family	Bootlace Terminals
Material	Copper (CU)
Colour	Silver-matt (MTSR)
Application Range	Low Voltage
Conductor Size (mm²)	0.75 mm ²
Diameter (D)	2.2 mm
Length (L)	8 mm
Length (L2)	7.3 mm
Max Voltage	600 V
Operating Temperature	-55 °C to +155 °C
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
Ø (D2)	1.2 mm
ROHS compliant	Yes

