

# vacuum suction cup ESV-20-CN

Part number: 191071

FESTO

Wearing part, easily replaceable



## Data sheet

Feature	Value
Suction cup height compensator	7 mm
Min. workpiece radius	50 mm
suction cup diameter	20 mm
suction cup volume	2.75 cm <sup>3</sup>
Position of connection	on top
Assembly position	Any
Suction cup shape	Round, bellows, 3.5 convolutions
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
Food-safe	See Supplementary material information
Ambient temperature	-10 ... 70 °C
Retention force at nominal operating pressure	8.2 N
Product weight	2.1 g
Colour	Black
Shore hardness	50 +/- 5
Materials note	Free of copper and PTFE Conforms to RoHS
Material suction cup	NBR