

Han TC100 male contact 35 mm² (Han K6/6)



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 000 6529
Specification	Han TC100 male contact 35 mm ² (Han K6/6)
HARTING eCatalogue	https://harting.com/09110006529

Identification

Category	Contacts
Series	TC 100
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Male
Manufacturing process	Turned contacts
Details	Only for use in the Han [®] K 6/6

Technical characteristics

Conductor cross-section	35 mm ²
Rated current	≤100 A
Contact resistance	≤0.3 mΩ
Stripping length	16 mm
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight



Pushing Performance
Since 1945

Material properties

ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	10
Net weight	24 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140188204
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522