



Main

| | |
|---------------------------|-------------------------------------|
| Range of product | Series 56 |
| Range | Clipsal - 56 Series |
| Product brand | Clipsal |
| Product or component type | Switch |
| Device presentation | Basic element with full cover plate |
| Device application | Control |
| Colour | Cover: grey |
| Handle colour | Grey |
| Suitability for isolation | No |

Complementary

| | |
|--------------------------------|--------------------|
| Switch function | 1-pole |
| Poles description | 1P |
| Actuator | Key |
| Control type | Rotary knob |
| Number of poles | 1 |
| Device mounting | Surface |
| Fixing mode | By screws |
| Material | PC (polycarbonate) |
| Tightening torque | 0.8 N.m |
| Local signalling | without |
| [Ue] rated operational voltage | 250 V AC 50 Hz |
| Rated current | 15 A |
| Breaking capacity | 15 kA |
| Motor M-rating AS3133 | M80 at 250 V |
| Rotary handle padlocking | 2 padlocks 8 mm |
| Marking | ON-OFF |
| Marking location | Marking on surface |
| Height | 107 mm |
| Width | 101 mm |
| Depth | 87 mm |
| Net weight | 0.383 kg |
| Targeted country | Australia |

Environment

| | |
|---------------------------------------|-----------------------------|
| Ambient air temperature for operation | -25...75 °C |
| IP degree of protection | IP66 conforming to AS 60529 |
| Standards | AS/NZS 3133 |

Packing Units

| | |
|------------------|----------|
| Package 1 Weight | 0.383 kg |
|------------------|----------|

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |