

FEATURES

- Voltage of 220V to 260V
- Lamp base of BA 15d
- Current rating of 38mA
- Diameter of 16mm
- Lamp size of T16
- Length of 35 mm
- Clear
- Luminosity of 30 lm
- Provides 3000 hours of lighting (from a stabilised 50Hz ac supply)

BA15d Indicator Light, Clear, 220 → 260 V, 38 mA, 3000h

RS Stock No.: 360-7496



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Incandescent Light Bulbs



Product Description

Looking for a high-performing bulb? The RS PRO BA15d clear indicator light is designed to provide a reliable source of illumination. It's suited to a range of industrial uses such as warning or signal lighting.

This T16 indicator light is a bi-pin bulb, so there are two pins at the base, and it provides 30 lumens of output.

General Specifications

Lamp Base	BA15d
Lamp Size	T16
Lens Colour	Clear
Luminosity	30lm ±20%
Life hours	3000h
Filament Type	Vacuum Type CC-7A
Housing Material	Glass
Applications	Automotive industry; Gambling machine industry; Car indicator; Garden lights; Paper lanterns; Battery-powered flashlights, warning or signal lighting

Electrical Specifications

Voltage Rating	220V to 260V
Current Rating	38mA
Wattage	10W
MSCP	2.8CP + 20%
Light Output	30lm
Operating Frequency	50Hz



Mechanical Specifications

Diameter	16mm
Length	35mm

Operation Environment Specifications

Ambient Operating Temperature	+20°C to +25°C
-------------------------------	----------------





Technical Drawing:

