

HC-B-G-MULTI01-PLBK - Cable gland



1345613

<https://www.phoenixcontact.com/in/products/1345613>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



EVO plastic cable gland with bayonet lock, for housing series B, cable diameter 6 x 6 mm ... 10 mm

Commercial data

Item number	1345613
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	AF7APL
GTIN	4063151658793
Weight per piece (including packing)	76.5 g
Weight per piece (excluding packing)	22.22 g
Country of origin	PL

HC-B-G-MULTI01-PLBK - Cable gland



1345613

<https://www.phoenixcontact.com/in/products/1345613>

Technical data


Product properties

Product type	Cable gland with bayonet locking
No. of conductors	6
Shielded	no

Connection data

Tightening torque	0.5 ... 0.8 Nm
-------------------	----------------

Dimensions

Dimensional drawing	
Width	72 mm
Height	95 mm
Length	53 mm

Material specifications

Color	black (RAL 9005)
Material Screw connection	PA
Flammability rating according to UL 94	V0 (Seal) V2 (Housing)
Seal material O-ring	NBR
Seal material Cable seal	NBR
Material for screw connection	PA

Cable/line

External cable diameter Cable 1	6 mm ... 10 mm
External cable diameter Cable 2	6 mm ... 10 mm
External cable diameter Cable 3	6 mm ... 10 mm
External cable diameter Cable 4	6 mm ... 10 mm
External cable diameter Cable 5	6 mm ... 10 mm
External cable diameter Cable 6	6 mm ... 10 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
Ambient temperature (operation)	-40 °C ... 100 °C

HC-B-G-MULTI01-PLBK - Cable gland



1345613

<https://www.phoenixcontact.com/in/products/1345613>

Mounting

Assembly note	Bayonet locking max. 3x can be removed
---------------	--

HC-B-G-MULTI01-PLBK - Cable gland


1345613

<https://www.phoenixcontact.com/in/products/1345613>



Drawings

Dimensional drawing



Dimensional drawing

HC-B-G-MULTI01-PLBK - Cable gland



1345613

<https://www.phoenixcontact.com/in/products/1345613>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1345613>



cUL Recognized
Approval ID: E255026



UL Recognized
Approval ID: E255026

HC-B-G-MULTI01-PLBK - Cable gland



1345613

<https://www.phoenixcontact.com/in/products/1345613>

Classifications

ECLASS

ECLASS-13.0	27140801
ECLASS-11.0	27440205

ETIM

ETIM 9.0	EC000441
----------	----------

HC-B-G-MULTI01-PLBK - Cable gland



1345613

<https://www.phoenixcontact.com/in/products/1345613>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

HC-B-G-MULTI01-PLBK - Cable gland

1345613

<https://www.phoenixcontact.com/in/products/1345613>



Accessories

TSD-M 1,2NM - Torque screwdriver

1212224

<https://www.phoenixcontact.com/in/products/1212224>



Torque screw driver, accuracy as per EN ISO 6789 standard, adjustable from 0.3 - 1.2 Nm

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in