

1595

## screw clamps

|  | art.      | A<br>~ | A max<br>mm | L<br>mm |
|---------------------------------------------------------------------------------|-----------|--------|-------------|---------|
| 015950020                                                                       | 1595 200  | 200    | 230         | 100     |
| 015950025                                                                       | 1595 250  | 250    | 270         | 120     |
| 015950030                                                                       | 1595 300  | 300    | 330         | 120     |
| 015950040                                                                       | 1595 400  | 400    | 420         | 120     |
| 015950050                                                                       | 1595 500  | 500    | 520         | 125     |
| 015950060                                                                       | 1595 600  | 600    | 620         | 125     |
| 015950080                                                                       | 1595 800  | 800    | 820         | 125     |
| 015950100                                                                       | 1595 1000 | 1000   | 1030        | 125     |

