VDE Diagonal Cutter 145mm

VDE DIAGONAL CUTTERS

- VDE (DIN EN/IEC 60900) certified tools. Tested to 10,000 volts and guaranteed to 1,000 volts. Tested against cold to -40°.
- Steel blades are fully forged, hardened and tempered for best durability. Grey titanium surface finish is non reflective and ensures maximum corrosion resistance.
- Induction hardened cutting edges to cut even the hardesst of materials.
- Precision machined joint for maximum power transmission with optimum leverage for easy and effortless work.
- Ergonomic grip with softgrip for comfortable handling and good grip.



Article Number	4932464566
Capacity [mm]	-
Capacity Pipe [Max. ⌀ mm]	-
Cutting capacity in cable Al and Cu [Max. Ø mm]	8
Cutting capacity in hard wire 1800N|mm^2 [Max. Ø mm]	1.7
Cutting capacity in soft wire 220N|mm^2 [Max. Ø mm]	5
Cutting capacity in very hard wire 2300N|mm^2 [Max. Ø mm]	-
Length (mm)	145
Pack quantity	1
Total length (mm)	145