



ITEM	Q'TY	PART NUMBER	PART DESCRIPTION	T
1	1	LPR2-XXX-XXX	Surface Mount Right Angle Light Pipe, 2.8mm, 2 Station. See Table on 2nd Page	
2	1	RLPH2-XXX	LPR Housing, 2 Station, White. See Table on 2nd Page	]




REV.	DESCRIPTION	DATE	APPROVED
Α	Engineering Release	11/06/09	T. Y.
В	Added Overall Height "K" Dim	03/04/11	T. Y.
ပ	Added Overall Snap Height Dimension	08/15/12	T. Y.









REV.	DESCRIPTION	DATE	APPROVED
	SEE SHEET #1		

RLP2-XXX-XXX						
ASSY P/N	Н	L	K	LPR2-XXX-XXX	RLPH2-XXX	FIGURE
RLP2-200-500	0.197 [5.0mm]	0.551 [14.0mm]		LPR2-200-500	RLPH2-200	
RLP2-200-650		0.669 [17.0mm]	0.287 [7.3mm]	LPR2-200-650	RLPH2-200	
RLP2-200-800		0.787 [20.0mm]		LPR2-200-800	RLPH2-200	
RLP2-400-500	0.394 [10.0mm]	0.551 [14.0mm]		LPR2-400-500	RLPH2-400	
RLP2-400-650		0.669 [17.0mm]	0.484 [12.3mm]	LPR2-400-650	RLPH2-400	
RLP2-400-800		0.787 [20.0mm]		LPR2-400-800	RPH2-400	
RLP2-600-500		0.551 [14.0mm]		LPR2-600-500	RLPH2-600	
RLP2-600-650	0.591 [15.0mm]	0.669 [17.0mm]	0.681 [17.3mm]	LPR2-600-650	RLPH2-600	
RLP2-600-800		0.787 [20.0mm]		LPR2-600-800	RLPH2-600	

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED) DECIMALS ANGULAR 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974 .X ± .1 X° ±1° .XX ± .01 TITLE:  $\bigoplus$ RIGHT ANGLE LIGHT PIPE, XXX ± 010 2.8MM, 2 STATION DESIGNED: REVISION: DATE: PART NO: RLP2-XXX-XXX

Raffy Paje 11/06/09 CHECKED:

DATE: CAGE CODE : 32559 | SHEET # 2 OF 2 T. Yin 11/06/09 CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.