

18V / 14.4V Portable Fan LXT

DCF203Z

Model DCF203 is a cordless fan powered by 14.4V/18V LXT battery and also compatible with AC power.

Run time with 18V 6.0Ah battery

- With Oscillation (H/M/L) = 410 / 650 / 1,010 mins
- Without Oscillation (H/M/L) = 430 / 700 / 1,155 mins



TECHNICAL SPECIFICATIONS

Air Flow (H/M/L)	8.2 / 6.5 / 5.2 m ³ /min
Max Air Speed (Hi)	190 m/min
Max Air Speed (Lo)	120 m/min
Max Air Speed (Med)	150 m/min
Battery Type	Lithium-ion
Body only machine	✓
Battery Range	14.4 - 18 v
Diameter (D)	235 mm
Net weight	1.9 – 2.6 kg

USER BENEFITS

- Easily removable fan cover for convenient clean-up
- Quiet running: Wind noise level has been reduced thanks to redesigned fan and fan cover
- Automatically swings 45° L/R
- Fan head angle can be adjusted from side to side and up and down (Up 90°, Down 45°, Right and Left 90°)
- 3-stage automatic timer with 1, 2, and 4 hour power-off selection
- 3x settings for optimal air velocity control
- Large carrying handle for easy handling
- Equipped with Battery protection circuit: designed to protect the battery from damages due to overdischarge, high temperature or overload current.

[Link to product - www.makita.com](http://www.makita.com)



RELATED PRODUCTS

(Recom

■ OTHER