



Demolition Hammer XGT®

HM002G

40Vmax X2 • SDS-MAX • 18 mm •
20.9 J

Cordless XGT® Demolition Hammer for professionals.

High power and compact design. Soft start suppresses start-up reaction for more control and better accuracy. Equipped with Anti-vibration technology (AVT). Equipped with Active feedback sensing technology (AFT). Auto-start wireless system (AWS). Variable speed control.



Technical specifications

Nominal Battery Voltage	2 x 40 V
Voltage XGT	✓
Brushless Motor	✓
Impacts per Minute (IPM)	950 - 1 900 min ⁻¹
Impact Energy	20,9 J
Adapted for SDS-MAX bits	✓
AWS ready	✓
Sound Power Level (L _{WA})	100,5 dB(A)
Sound Pressure Level (L _{pA})	91 dB(A)
Noise Uncertainty (K Factor)	1,9 dB(A)
Tool weight with battery	12,0 - 14,5 kg
Product Dimensions (L x W x H):	574 x 146 x 324 mm
Vibration Level, Chiselling with D-type Side Handle	6,6 m/s ²
Vibration Uncertainty (K Factor), Chiselling with D-type Side Handle	1,5 m/s ²

User benefits

- Vibration absorbing handle provides comfortable operation
- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work
- Soft start suppresses start-up reaction for more control and better accuracy
- 12 bit angle settings allow the bit to be set at different positions for operating convenience
- One touch sliding chuck enables quick and easy bit changes
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Constant speed control maintains constant speed under load

Link to product - www.makitauk.com



Related products

Optional AC

194683-7

Grease vessel set, 100 ml



198993-4
Grease vessel for bit 100 ml



199144-2

Dust Extraction Attachment



417003-1
Side Handle



443122-7

Cleaning Cloth



821848-5
Plastic Case



Other

User manual

Parts drawing