

FEATURES

- Swivel castor
- Medium-duty
- Load capacity of 125kg
- Wheel diameter of 100mm
- Overall height of 128mm
- Wheel width of 35mm
- Fixing plate dimensions of 102mm x 84mm
- White polypropylene tyres
- Fixing centres of 80mm x 60mm
- Top plate fitting
- Four 8mm fixing holes
- Plain bore hub bearing

RS PRO Swivel Swivel Castor, 125kg Load Capacity, 100mm Wheel Diameter

RS Stock No.: 828-6265



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Use this 100 mm swivel castor to move heavy objects like a piece of furniture or a workstation safely. It's easy to manoeuvre thanks to its full 360° motion and is capable of bearing loads up to 125 kg.

This castor's rectangular fixing plate offers a fast and easy mounting option for increased stability when transporting heavy loads. Its pressed-steel construction and plain bore bearing give this product a long operating life, while white polypropylene tyres offer increased durability and shock resistance. The tyres perform particularly well on softer indoor surfaces and won't mark hard floors.

General Specifications

Rotation	Swivel
Weight Class	Medium Duty
Load Capacity	125kg
Tyre Material	Polypropylene
Hub Material	Polypropylene
Includes Brake	No
Features	Top Plate Fitting
Applications	General Purpose

Mechanical Specifications

Mounting Type	Plate
Wheel Diameter	100mm
Wheel / Tread Width	35mm
Overall Height	128mm
Number of Fixing Holes	4
Fixing Hole Size	8mm
Hub Bearing Type	Plain Bore



Fixing Centres Specifications		
Fixing Centres	80mm x 60mm	
Fixing Centres (Length)	80mm	
Fixing Centres (Width)	60mm	

Fixing Plate Specifications		
Fixing Plate Dimensions	102mm x 84mm	
Fixing Plate Length	102mm	
Fixing Plate Width	84mm	





Specifi	cation
Application	General Purpose / Industrial
Features	Ball Bearing Swivel Head
Fixing Centres	80x60mm
Fixing Centres Length	80mm
Fixing Centres Width	60mm
Fixing Hole Size	8mm
Fixing Plate Dimensions	102x84mm
Fixing Plate Length	102mm
Fixing Plate Width	84mm
Hub Bearing Type	Plain
Hub Material	Polypropylene
Load Capacity	125kg
Number of Fixing Holes	4
Overall Height	128mm
Rotation	Swivel
Tyre Material	Polypropylene
Weight Class	Light Duty
Wheel Diameter	100mm
Wheel Width	35mm