

5904VG/3
Assortment of 132 tools

Car repairs

		art.
	059041062	5904VG/3



- n. 6 **31/B6N**: Ø 2÷8 mm
- n. 1 **32**: centre punch Ø 5 mm
- n. 1 **35**: flat chisels, ribbed type 200 mm
- n. 17 **42**: combination wrenches 6÷22 mm
- n. 8 **55**: double open end wrenches 6x7 - 8x9 - 10x11 - 12x13 - 14x15 - 16x17 - 18x19 - 20x22 mm
- n. 9 **96N/SC9**: offset hexagon key wrenches ○ 1,5 - 2 - 2,5 - 3 - 4 - 5 - 6 - 8 - 10 mm
- n. 11 **96T/SP11**: offset hexagon key wrenches ○ 2÷10 mm
- n. 13 **97TX/B13**: offset key wrenches for Torx® head screws ⚙ T6÷T50
- n. 1 **111E**: Adjustable wrench 300 mm
- n. 13 **920A/SB13**: 1/2" square drive hexagon sockets with rail ○ 10÷22 mm
- n. 1 **920/21**: 1/2" drive extension bar 125 mm
- n. 1 **920/22**: 1/2" drive extension bar 255 mm
- n. 1 **920/25**: 1/2" drive universal joint
- n. 1 **920/42**: 1/2" drive sliding T-handle
- n. 1 **920/50**: 1/2" push-through drive ratchet ⚙
- n. 6 **952**: T - handle wrenches with swivelling socket ○ 8 - 10 - 12 - 13 - 17 - 19 mm
- n. 1 **965**: pry bar with handle 450 mm
- n. 2 **1032**: circlip pliers straight, internal ○ 180 - 225 mm
- n. 2 **1034**: circlip pliers bent, internal ○ 170 - 210 mm
- n. 2 **1036**: circlip pliers straight, external ● 175 - 225 mm
- n. 2 **1038**: circlip pliers bent, external ● 175 - 220 mm
- n. 1 **1048N**: slip joint pliers, slip-proof PVC coated handles 250 mm
- n. 1 **1057A**: self - locking pliers 240 mm
- n. 1 **1084GBM**: heavy duty diagonal cutting nippers, bi-material handles, industrial finish ⚡ 200 mm
- n. 1 **1092V**: toggle lever assisted end cutting nippers ⚡ 200 mm
- n. 1 **1112**: tin snips 250 mm
- n. 1 **1128BMX**: electrician's scissors, straight blades 147 mm
- n. 1 **1150GBM**: heavy duty combination pliers, bi-material handles, industrial finish = 180 mm
- n. 4 **1260**: screwdrivers for slotted head screws ● 3x75 - 4x100 - 5,5x125 - 6,5x150 mm
- n. 1 **1260N**: screwdrivers for slotted head screws, extra-short series ● 6,5x30 mm
- n. 2 **1260E**: screwdrivers for slotted head screws with hexagon bolsters ● 8x175 - 10x200 mm
- n. 3 **1262**: screwdrivers for cross head Phillips® screws ⚙ PH0x100 - PH1x120 - PH2x100 mm
- n. 1 **1262N**: screwdrivers for cross head Phillips® screws, extra - short series ⚙