

Features

- 50° angled flush cutter, for specific electronics applications.
- Steel thickness 2.5mm.
- For copper wire Ø 1.30 mm (16 awg)
- Tool is equipped with a return spring designed to have a constant force, thus reducing operator effort.
- Ergonomic anti-slip bicomponent handle for a safe, light and comfortable grip
- Anti-reflection phosphating surface treatment
- Laser marking.
- Made in Italy.

RS PRO 50° angled flush cutter. Medium head.

Manufacturer Stock No.: (0429714)



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- *Made in Italy with high carbon steel and undergo a controlled atmosphere heat treatment.*
- *50° angled flush cutter for specific electronics applications. It can cut copper wire max Ø 1.30mm-16 awg.*
- *The anti-reflection phosphating surface treatment ensures an accurate view of the work being carried out.*
- *The tools are joined with grounded holes and surfaces, thereby allowing precise movements.*
- *The anti-slip bi-material dolphin handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator even when used constantly for many hours.*

General Specifications

Cutter Type	50° angled flush cutter. Medium head.
Material	High carbon steel
ESD Safe	NO

Mechanical Specifications

Cutting capacities	Ø 1.30mm (16 awg) copper wire
Cutting force	5 kg
Steel thickness	2.5 mm
Blade angle	50°
Overall Length	135 mm
Weight	75 g

