



Part Number : [1301460151](#)
Product Description : Watertite Extreme
Receptacle with Duplex Flip Coverplate with
Locking Blade, 2 Pole/3 Wire, NEMA L5-15,
125V
Series Number : 130146
Status : Active
Product Category : Wiring Devices
Engineering Number : 65W47DPLX



Documents & Resources

Drawings
[1301460151_sd.pdf](#)

3D Models and Design Files
[1301460151_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Receptacle with Duplex Flip Coverplate with Locking Blade, 2 Pole/3 Wire, NEMA L5-15, 125V
IP Rating	IP67
NEMA Configuration	NEMA L5-15
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678871443

Agency

CSA	LR6837
UL	E68122

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	125V

Physical

Cord Type	N/A
Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A

Lighted Connector	No
Locking Blade	Yes
Net Weight	485.343/g
Poles	2-pole/3-wire
Receptacle Type	Duplex

This document was generated on Mar 27, 2025