

Article data sheet



MOTION STATIC mobile stand fixed height

- Contemporary design that fits perfectly in any modern office space
- VESA head for screen and accessories can be easily adjusted to any height during installation
- Stand is delivered as an assembly kit and is very easy to setup (<15 minutes)
- Easy to move system provides perfect mobility
- Optional accessory shelves for e.g. videoconferencing cameras and laptops are available. These come with a VESA 100 mount on the bottomside for small form factor PC's or wireless screensharing hardware

Highlights

- Fixed height mobile column system
- VESA 200x200 up to 800X600 display interface
- Easy to assemble
- Mobile stand with high stability
- Total height 174 cm
- 8 years of warranty on the entire solution

Accessories

- MOTION STATIC accessory shelf large natural beech (Art.No. 7-811971)

Art.No. **7-811431**

GTIN **8713797104821**





Height adjustable	No
Mounting interface	VESA 200x200 up to VESA 800x600
Package contents	Mounting material, Mounting instruction, Mobile stand
Maximum screen weight	120.00 kg
Maximum screen size	98 "
Cable lock slot	No
Cable compartment	No
Product warranty	8 years

GTIN	8713797104821
Article number	7-811431
Customs tariff number	940310980000
Quantity	1 piece
Packing dimensions	777 x 525 x 1605 mm
Weight (gross/net)	44.08 kg / 41.26 kg

Article data sheet

Product overview

Article name	Article number	GTIN/EAN	Minimum order quantity
Legamaster MOTION STATIC mobile stand fixed height	7-811431	8713797104821	1