



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought




TE Part #280509-2
2X09 POS .100DR MODU-



TE Part #1419108-1
RT114012




TE Part #1393258-2
V23047-A1005-A501




TE Part #280375-2
15P AMPMODU II SHRD HDR, ST, 0.38 AU





TE Part #2071452-9
RZ0H-1A4-D012-R0001 (TES)



TE Part #280371-2
4P AMPMODU II SHRD HDR, ST, 0.38 AU



TE Part #280385-2
2X8P AMPMODU II SHRD HDR,ST,0.38 AU



TE Part #6-440052-3
2.5MM,HDR,3POS,VERTICAL CONN W /O REGRIND



TE Part #3-282837-2
TERMI-BLOK,PCB,13P,INKSTAMP



TE Part #3-282837-3
TERMI-BLOK,PCB,9P,INKSTAMP

Documents

Product Drawings
A/L UNIV HDR 26P VERT SHT LAT
English

Product Specifications
Product Specification
English

Agency Approvals
UL Report
English