


FEATURES

- **Non-Dimmable:** Simplifies installation and reduces compatibility issues with dimming systems
- **2.5 A Driver Current:** Provides sufficient current for efficient LED operation
- **198-264 V AC Input Voltage:** Compatible with a wide range of AC power sources
- **IP67 Rating:** Offers excellent protection against dust and water, ideal for outdoor or industrial use
- **Constant Voltage Operation:** Ensures consistent light output and performance
- **Single Output:** Simplifies wiring and installation
- **60 W Maximum Output Power:** Supports a variety of LED configurations

RS PRO 60W LED Driver, IP67 Constant Voltage

RS Stock No: 642-781



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 60W LED Driver is designed to provide reliable power to LED lighting systems. With a constant voltage output of 24 V, it ensures stable performance for various lighting applications. Its robust design and IP67 rating make it suitable for use in challenging environments, offering protection against dust and water ingress.

General Specifications

Dimming Operation	Non-Dimmable
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver

Electrical Specifications

Driver Current	2.5 A
Input Voltage	198-264 V ac
Input Voltage Type	AC
Maximum Output Power	60 W
Output Voltage	24 V

Protection Category

IP Rating	IP67
-----------	------

Approvals

Standards/Approvals	CE, EEN 55015, EN 61000-3-2, EN 61000-3-3, EN 61547, EN61000-4-2,3,4,5,6,8,11, EN61347-1, EN61347-2-13
---------------------	--