

HSS-Co twist drill bits

PRO Stainless Steel HSS-Co Twist Drill Bit

PRO

- For drilling in steel and stainless steel, eg when pre-drilling profiles and beams for anchors, rivets, threads, and fixtures
- Highly efficient for construction workers and installers: Long Life
- Designed for drilling in stainless steel
- Cylindrical shank compatible with three-jaw drill chucks



PRODUCT PROPERTIES						ORDERING INFORMATION				
Diameter (D) mm	Working length mm	Total length mm	Diameter (D) Inch	Shank diameter (d) mm	Shank diameter (d) Inch	Packaging type	Pack quantity	Minimum order quantity	Barcode	Part number
Pack of 1										
1	12	34	-	10	-	C1f	1	5	6949509242983	2 608 577 587
1.5	18	40	-	10	-	C1f	1	5	6949509242990	2 608 577 588
2	24	49	-	10	-	C1f	1	5	6949509243003	2 608 577 589
2.5	30	57	-	10	-	C1f	1	5	6949509243010	2 608 577 590
3	33	61	-	10	-	C1f	1	5	6949509243027	2 608 577 591
3.2	36	65	-	10	-	C1f	1	5	6949509243034	2 608 577 592
3.3	36	65	-	10	-	C1f	1	5	6949509243041	2 608 577 593
3.5	39	70	-	10	-	C1f	1	5	6949509243058	2 608 577 594
4	43	75	-	10	-	C1f	1	5	6949509243065	2 608 577 595
4.1	43	75	-	10	-	C1f	1	5	6949509243072	2 608 577 596
4.2	43	75	-	10	-	C1f	1	5	6949509243089	2 608 577 597
4.5	47	80	-	10	-	C1f	1	5	6949509243096	2 608 577 598
4.8	52	86	-	10	-	C1f	1	5	6949509243102	2 608 577 599
5	52	86	-	10	-	C1f	1	5	6949509243119	2 608 577 600
5.1	52	86	-	10	-	C1f	1	1	6949509243126	2 608 577 601
5.2	52	86	-	10	-	C1f	1	5	6949509243133	2 608 577 602
5.5	57	93	-	10	-	C1f	1	5	6949509243140	2 608 577 603
6	57	93	-	10	-	C1f	1	1	6949509243157	2 608 577 604
6.5	63	101	-	10	-	C1f	1	5	6949509243164	2 608 577 605
6.8	69	109	-	10	-	C1f	1	5	6949509243171	2 608 577 606
7	69	109	-	10	-	C1f	1	5	6949509243188	2 608 577 607
7.5	69	109	-	10	-	C1f	1	1	6949509243195	2 608 577 608
8	75	117	-	10	-	C1f	1	5	6949509243201	2 608 577 609
8.5	75	117	-	10	-	C1f	1	5	6949509243218	2 608 577 610
9	81	125	-	10	-	C1f	1	5	6949509243225	2 608 577 611
9.5	81	125	-	10	-	C1f	1	1	6949509243232	2 608 577 612
10	87	133	-	10	-	C1f	1	1	6949509243249	2 608 577 613
Pack of 1 reduced shank to 10 mm or 3/8"										
10.2	87	133	-	10	-	C1f	1	5	6949509243256	2 608 577 614
10.5	87	133	-	10	-	C1f	1	1	6949509243263	2 608 577 615
11	94	142	-	10	-	C1f	1	5	6949509243270	2 608 577 616
11.5	94	142	-	10	-	C1f	1	1	6949509243287	2 608 577 617
12	101	151	-	10	-	C1f	1	5	6949509243294	2 608 577 618
12.5	101	152	-	10	-	C1f	1	1	6949509243300	2 608 577 619
13	101	152	-	10	-	C1f	1	5	6949509243317	2 608 577 620
Pack of 10										
1	12	34	-	-	-	P2a	10	1	3165140521079	2 608 585 872
1.5	18	40	-	-	-	P2a	10	1	3165140521086	2 608 585 873
2	24	49	-	-	-	P2a	10	1	3165140521093	2 608 585 874
2.5	30	57	-	-	-	P2a	10	1	3165140521109	2 608 585 875
3	33	61	-	-	-	P2a	10	1	3165140521116	2 608 585 876
3.2	36	65	-	-	-	P2a	10	1	3165140521123	2 608 585 877
3.3	36	65	-	-	-	P2a	10	1	3165140521130	2 608 585 878
3.5	39	70	-	-	-	P2a	10	1	3165140521147	2 608 585 879
4	43	75	-	-	-	P1h	10	1	3165140521154	2 608 585 880
4.1	43	75	-	-	-	P1h	10	1	3165140521161	2 608 585 881
4.2	43	75	-	-	-	P1h	10	1	3165140521178	2 608 585 882