

Cisco SFP-GE-T Compatible SFP Transceiver Module - 1000BASE-T

Product ID: SFPC1110



The SFPC1110 is a Cisco SFP-GE-T compatible copper transceiver module that has been designed, programmed and tested to work with Cisco® brand switches and routers. It delivers dependable 1GbE (1000 Mbps) connectivity over copper cable, for 1000BASE-T compliant networks, with a maximum distance of up to 100 m (328 ft).

Technical Specifications:

- **Maximum Data Transfer Rate:** 1.25 Gbps
- **Type:** Copper
- **Connection Type:** RJ45 Connector
- **Maximum Transfer Distance:** 100 m (328 ft)
- **MTBF:** 4,655,371 hours
- **Power Consumption:** Less than 1.3 Watts
- **Digital Diagnostics Monitoring (DDM):** No

This SFP copper module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

StarTech.com SFPs

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

- Replacing defective or damaged SFP modules in Cisco switches and routers
- Expand your network to remote segments

Features

- 100% compatibility with Cisco SFP-GE-T guaranteed
- StarTech.com SFP modules are backed by a lifetime warranty
- Uses a cost-effective cabling alternative to fiber-optic set ups
- Meets or exceeds OEM specifications and Multi-Source Agreement (MSA) industry standards
- Low power consumption of less than 1.3 W
- Hot-swappable with fiber-optic modules

Hardware	Warranty	Lifetime
	Compatible Brand	Cisco
	Industry Standards	IEEE 802.3ab 1000BASE-T
Performance	Auto MDIX	Yes
	Compatible Networks	1000 Mbps (1 Gbps)
	DDM	No
	Max Transfer Distance	100 m (328 ft)
	Maximum Data Transfer Rate	1.25 Gbps
	MTBF	4,655,371 hours
	Type	Copper
Connector(s)	Local Unit Connectors	1 - RJ-45 Female
Power	Power Consumption (In Watts)	< 1.3 W
Environmental	Humidity	30~70% RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-40°C to 85°C (-40°F to 85°F)
Physical Characteristics	Product Height	0.5 in [13 mm]
	Product Length	2.8 in [70 mm]
	Product Weight	1.6 oz [46 g]
	Product Width	0.5 in [13 mm]
Packaging Information	Shipping (Package) Weight	1.9 oz [55 g]
What's in the Box	Included in Package	1 - 10/100/1000 Mbps RJ45 SFP

Product appearance and specifications are subject to change without notice.