

# Switch Mode Power Supply

## ATX12V v.2.2~ 12cm fan Active PFC



Dimension: L150 x W140 x H86mm  
(5.9" x 5.5" x 3.4")



### Features

- Specification compliance: ATX12V v2.2 & EPS12V v2.9
- Support the latest Intel & AMD Socket
- PCI Express & Serial ATA ready
- Double forward converter circuit
- High efficiency and reliability
- Low ripple & noise
- Super low noise fan control
- Short circuit protection on all outputs
- Over voltage protection
- Over power protection
- 100% hi-pot test
- 100% burn in, high temperature cycled on/off

### AC input voltage & DC output

Model	DC output						Input voltage		
	+3.3V	+5V	+12V1	+12V2	-12V	+5Vsb	Total power	Full range	Fixed 220V
SS-500ET Active PFC	24A	24A	17A	17A	0.8A	2.5A	500W	Yes	Yes
	130W Max <sup>1</sup>		409W <sup>2</sup>		9.6W	12.5W			
SS-400ET Active PFC	20A	20A	17A	17A	0.8A	2.5A	400W	Yes	Yes
	130W Max <sup>1</sup>		360W <sup>2</sup>		9.6W	12.5W			
SS-350ET Active PFC	20A	20A	17A	17A	0.8A	2.5A	350W	Yes	Yes
	130W Max <sup>1</sup>		324W <sup>2</sup>		9.6W	12.5W			
SS-300ET Active PFC	18A	20A	17A	17A	0.8A	2.5A	300W	Yes	Yes
	120W Max <sup>1</sup>		288W <sup>2</sup>		9.6W	12.5W			

Remarks: 1. Combined +3.3VDC & +5V DC maximum power

specification may change without prior notice

### Electrical Specification

Input frequency:	47/63Hz	
In-rush current, cold start:	100A max.	
Hold up time, full load:	10ms. typical	
Efficiency:	at normal input voltage	>70%
	at AC 110v 60Hz	75% typical
	at AC 220v 50Hz	78% typical
Optional 80PLUS	at normal input voltage	>80%
Line regulation:	+/- 1% typical	
Load regulation:	+/- 5% typical	
Cross regulation:	+/- 5% typical	
Ripple / noise:	1%	
Standby mode	<5W	
MTBF, full load @ 25°C amb. Excluding the DC fan:	>100k hrs	
Power Factor Correction: Active PFC	99% typical	

### Safety compliance

CUL, TUV, CB, CCC

### EMI/RFI compliance

CE, FCC, C-tick

ISO 14001



REGISTERED FIRM



REGISTERED FIRM

www.seasonic.com

### Sea Sonic Electronics Co., Ltd.

#### Head Office:

8F, #19, Alley 360, Sec. 1, Neihu Road, Neihu, Taipei, Taiwan, R.O.C.

Tel: +886 2 2659 0338

Fax: +886 2 2659 0530

sales@seasonic.com.tw

www.seasonic.com

#### Factories:

I. Tao Yuan, Taiwan.

II. Dong Guan, China.

#### USA office:

Tel: +1 626 969 9966

Fax: +1 626 969 9986

usa@seasonic.com