




PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 8:30 (UTC)



6903ZZ

Single-Row Deep Groove Ball Bearings



Boundary Dimensions

d	17	mm	Bore diameter
D	30	mm	Outside diameter
B	7	mm	Width
r (min.)	0.3	mm	Chamfer dimension

Basic Load Ratings

Cr	5050	N	Basic dynamic load rating
C0r	2550	N	Basic static load rating

Speeds

Grease	24000	min-1	Grease lubrication
--------	-------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	19	mm	Diameter of shaft abutment
da (max.)	19.5	mm	Diameter of shaft abutment
Da (max.)	28	mm	Diameter of housing abutment
ra (max.)	0.3	mm	Radius of shaft or housing fillet

Calculation factors

fo	14.7		Factor
----	------	--	--------

Additional information

z	11		Number of Balls
Dw	3.969	mm	Ball Diameter

Mass

Mass approx.	0.017	kg	Mass approx.
--------------	-------	----	--------------

