

PWKO-05040 - PWKO

General Part Information	
Product Description	PWKO-05040
Article Number	69749
POPNut Type	PWKO
Standard Bulk Pack Quantity	8,000

Geometry / Dimensions	
Thread Size	M5
Body Type (open / closed)	Open
Body Features	Round
Body Length (mm)	13.80
Min. Grip Thickness (mm)	1.50
Max. Grip Thickness (mm)	4.00
Head Style	Countersunk
Hole Diameter (mm)	7.00
Head Diameter (mm)	9.50
Head Thickness (mm)	1.40
Barrel Diameter (mm)	6.90

Material / Weight	
Material	Stainless Steel 316
Weight per thousand (kg)	2.0

