



## MECCA PRO 1/2" DEEP IMPACT SOCKET SET DIN AF 18 PIECES

- 14 deep imperial sockets from 3/8" to 1-1/4"
- Retaining pins (2 pcs) and rings (2 pcs) included
- Made of chrome molybdenum (CR-MO)
- For use with power tools
- Supplied in a robust blow moulded box

Impact Socket Set 1/2" Drive AF Deep DIN 18 Pieces

### General information

**Country of origin:** Taiwan  
**Barcode:** 5020385020429  
**Tarriff code Europe:** 8204200000  
**ECCN US:** EAR99  
**UNSPSC:** 27111703

### Dimensions

**Net weight (g):** 4200  
**Width (mm):** 369  
**Depth (mm):** 185  
**Height (mm):** 85

### Attributes

**Product type:** Impact Tool Sets  
**Certificates:** N/A  
**Number of pieces:** 18  
**Drive:** 1/2"  
**Socket type:** Deep, 6-point  
**Standard type:** DIN  
**Unit of measurement:** AF

### Features



**DESIGNED IN SWEDEN**

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3  
441 39 Alingsås, Sweden

# LIST OF CONTENTS



## **T9218LAF** MECCA PRO 1/2" Deep Impact Socket Set DIN AF 18 Pieces

- 920212** 1/2" Deep Impact Socket DIN AF 3/8"
- 920214** 1/2" Deep Impact Socket DIN AF 7/16"
- 920216** 1/2" Deep Impact Socket DIN AF 1/2"
- 920218** 1/2" Deep Impact Socket DIN AF 9/16"
- 920220** 1/2" Deep Impact Socket DIN AF 5/8"
- 920222** 1/2" Deep Impact Socket DIN AF 11/16"
- 920224** 1/2" Deep Impact Socket DIN AF 3/4"
- 920226** 1/2" Deep Impact Socket DIN AF 13/16"
- 920228** 1/2" Deep Impact Socket DIN AF 7/8"
- 920230** 1/2" Deep Impact Socket DIN AF 15/16"
- 920232** 1/2" Deep Impact Socket DIN AF 1"
- 920234** 1/2" Deep Impact Socket DIN AF 1-1/16"
- 920236** 1/2" Deep Impact Socket DIN AF 1-1/8"
- 920240** 1/2" Deep Impact Socket DIN AF 1-1/4"
- O92194** Retaining Ring 19 × 4.0 mm
- O92244** Retaining Ring 24 × 4.0 mm
- P92320** Retaining Pin 3 × 20 mm
- P92325** Retaining Pin 3 × 25 mm