

JS.T – 3/8" Slotted Head Bit Sockets



Description:

- **HIGH PERFORMANCE** - Designed and manufactured for extremely high tightening forces
- **BIT PROFILE** - For Female drive Fasteners
- **NECK-DOWN DESIGN** - Facilitating the use in narrow spaces
- **Matte finish**
- **ISO 2725-1 - DIN3124 – ISO 1174-1**

	Fastener Head Size (mm)	Square Drive	Diameter (mm)	Length (mm)	Weight (g)
JS.5.5T	5.5	3/8"	17.9	50	33
JS.7T	7	3/8"	17.9	50	34
JS.8T	8	3/8"	17.9	50	43