

FEATURES

- 40 micron filtration
- Manual drain
- With square gauge
- Complete with bracket

RS PRO

Filter / Regulator / Lubricator

RS Stock No.: 2351092



Manual Drain
Supplied with Bracket and Square Gauge

Product Description

Part No.	Body Size	Port Size	Flow Rate
2351092	2000	1/4"	1200 l/min



Features

- 40 micron filtration
- Manual drain
- With square gauge
- Complete with bracket

General Specifications

Maximum working pressure	10 bar
Working temperature	-5°C to +60°C (no freezing)
Filter precision	40 micron
Working medium	Clean air (after 40 micron filtration)
Maximum inlet pressure	15 bar
Adjustable pressure range	1.5 to 9 bar

Materials	
Body	Aluminium
Bowl	Polycarbonate

Similar Products

Part No.	Body size	Port Size	Flow Rate
2351093	3000	1/2"	2400 l/min
2351094	4000	1/2"	1400 l/min
2351095	4000	1/2"	1400 l/min