



Main

Range	New Unica
Product or component type	Workstation
Number of modules	4 x 4 modules
Mounting position	Vertical
Fixing mode	Screws

Complementary




Provided equipment	Fixing frame Cover frame
Device mounting	Surface
Cable entry	5 removable plates 2 bottom cable entries 20 mm for diameter 2 bottom cable entries 25 mm for diameter 2 bottom cable entries 45 mm for diameter
Material	ABS (acrylonitrile butadiene-styrene): box ABS (acrylonitrile butadiene-styrene): separator ABS (acrylonitrile butadiene-styrene): cover frame
Depth	60 mm
Width	300 mm
Height	165 mm
Net weight	0.635 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IK degree of protection	IK04
-------------------------	------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes

RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Minimum percentage of recycled plastic content	69